

# Parscan 48V Zoom spotlight













A1000065 Silver LED module: 5.7W 611lm 2700K warm white Casambi Bluetooth

Casambi Bluetooth Version 1 Size S Zoom lens oval

### Product description

Housing: cast aluminium, powder-coated; can be swivelled through 90° on the bracket. Upper cover made of polymer.

Bracket: cast aluminium/polymer, coated; can be rotated through 360° on the adapter.

Minirail adapter for ERCO Minirail 48V track: polymer, black.

ERCO control gear. Add-on control unit: Casambi

Bluetooth.

LED module: high-power LEDs. Collimating lens made of optical polymer. Lens unit: polymer, black, rotatable through 360°. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.

Control via Casambi app (Android/ iOS) with Bluetooth Low Energy (BLE)capable mobile devices or "Casambi Ready" products.

Ready" products. Protection Class III Weight 0.30kg

60°	60°>
Co-C <sub>180</sub> — C <sub>90</sub> -C <sub>270</sub> —	
730°	30°5
75	0 cd

60°	60°×
Co-C <sub>180</sub> ————————————————————————————————————	
/ 230°	30°(
400	cd

h(m)	E(Ix)	D(m)		
		CO	C90	
		63°	25°	
1	609	1.23	0.44	
2	152	2.45	0.89	
3	68	3.68	1.33	
4	38	4.90	1.77	
5	24	6.13	2.22	

h(m)	E(Ix)	D(m)	
		CO	C90
		68°	65°
1	303	1.35	1.27
2	76	2.70	2.55
3	34	4.05	3.82
4	19	5.40	5.10
5	12	6.75	6.37

#### Technical data

Luminous flux of the luminaire	386lm
Connected load	6.5W
Luminaire efficacy	59lm/W
Colour deviation	1.5 SDCM
Colour rendition index	CRI 92
Lumen maintenance (LED manufacturer	L90/B10 ≤50000h
specifications)	L90 ≤100000h
LED failure rate	0.1% ≤50000h
Dimming range	0.1%-100%
Dimming method	CCR
LMF	E
Standby power per control gear	0.3W
Luminaires per circuit breaker B16	



**DALI controllable via accessory**DALI Casambi Gateway for controlling
Casambi Bluetooth via DALI.



Mounting Minirail 48V track Minirail 48V singlet

For your regional contact in the ERCO Sales network click here www.erco.com/contact

Technical Region: 220-240V 50/60Hz We reserve the right to make technical and design changes. Edition: 28.01.2023 Current version under www.erco.com/A1000065



# Parscan 48V Zoom spotlight

## Planning data

Melanopic light effect

 Art. no.
 Spectrum
 MR
 MDER

 A1000065 (direct)
 2700K CRI 92
 0.48
 0.43

MR Melanopic ratio according to DIN SPEC 5031-100-100:2015-08: "amel;v"

MDER Melanopic daylight equivalent ratio according to DIN SPEC 5031-100-100:2015-08: "amel;D65;v"

Multiplying the melanopic ratio MR with the illuminance gives the equivalent melanopic illuminance EML (equivalent melanopic lux). The equivalent illuminance with daylight (D65) is obtained by multiplying the illuminance by the melanopic daylight equivalent ratio MDER.

Cleaning (a)	1				2				3			
Ambient conditions	Р	C	N	D	Р	C	N	D	Р	C	Ν	D
LMF	0.96	0.94	0.90	0.86	0.93	0.91	0.86	0.81	0.92	0.90	0.84	0.79
RSMF	0.99	0.97	0.95	0.92	0.98	0.97	0.95	0.92	0.98	0.97	0.95	0.92
Hours of operation (h)	1000	5000	10000	20000	30000	40000	50000					
LLMF	1.00	0.99	0.98	0.96	0.94	0.92	0.90					
LSF	1	1	1	1	1	1	1					

MF LMFxRSMFxLLMFxLSF
MF Maintenance Factor
LMF Luminaire Maintenance Factor
RSMF Room Surface Maintenance Factor
LLMF Lamp Lumens Maintenance Factor

LSF Lamp Survival Factor
P Room pure
C Room clean
N Room normal
D Room dirty

Data according to regulations

2019/2020/EU supplemented by 2021/341/EU and 2019/2015/EU supplemented by 2021/340/EU Energy Consumption Labelling Ordinance

This product contains a light source of efficiency class F

Due to thermal and photometric properties as well as to protect electronic components from ESD (electrostatic discharge) the light source cannot be changed by the customer.

ID EPREL: 985713

Model identifier: 3000057843

Download data sheets for control gear and disassembly instructions at

www.erco.com/slr

### Technical data in accordance with international norms and standards

IEC 60598 Luminaires – Part 1+2: general requirements, specific

requirements and tests

IEC 62031 LED modules for general lighting – safety requirements IEC 62471 Photobiological safety of lamps and lamp systems EN13032-4 Light and lighting – measurement and representation of

photometric data

CIE 13 Method of measuring and specifying colour rendering


properties of light sources

All technical data is subject to industry-standard tolerances. Also see www.erco.com/erco-led

For explanations of the symbols and abbreviations used and other general information, see www.erco.com/symbols

# Parscan 48V Zoom spotlight


### Accessories



#### AC002064

Lens unit spot Polymer, black lacquered, rotatable through 360°. Replacement without tools.


Spherolit lens made of optical polymer.



#### AC002065

Lens unit wallwash Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.



#### AC002062

Lens unit flood Polymer, black lacquered, rotatable through 360°. Replacement without


Spherolit lens made of optical polymer.



#### AC002122

Lens unit zoom spot Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus



#### AC002060

Lens unit wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.


Spherolit lens made of optical polymer.



#### AC002123

Lens unit zoom oval Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



#### AC002063

Lens unit extra wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.


Spherolit lens made of optical polymer.



#### AC00226

Lens unit narrow framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools.

Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black.
Aperture.



#### AC002061

Lens unit oval flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.




#### AC002266

Lens unit wide framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools.

2 projection lenses, continuously focusable. Ideal for short projection distances.

Framing attachment: stainless steel, black.


Aperture.



#### AC002067

Lens unit oval wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.



#### AC006002

Softening lens

Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

# Parscan 48V Zoom spotlight

## Accessories




AC006025 Sculpture lens Filter holder: polymer, black, rotatable through 360°. Replacement without



AC006013 Fish Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006009 Cold Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006010 Marbled Meat Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006007 Cold Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006008
Bread and Pastry Filter
Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006005 Warm Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006004 Blue Light Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006003 Warm Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC001010 Snoot Polymer, black.




AC006006 Skintone Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.




AC004024 Honeycomb anti-glare screen Black

# Parscan 48V Zoom spotlight


### Accessories




AC005002 Barn doors 4-fold Aluminium, coated black.



AC007001 DALI Casambi Gateway Enables DALI systems to be connected to luminaires, sensors and control units with Casambi Bluetooth. The gateway can only be operated in Evolution networks. Power is supplied exclusively via the DALI bus. Connection via two lines which must be designed for mains voltage. The gateway requires no DALI addresses, the devices appear as non-configured devices in the DALI system. Addressing/commissioning is performed via the DALI control. It can individually control 64 devices, and via the broadcast command up to 249 devices.



AC005004 Barn doors 8-fold Aluminium, coated black.





Add-on Control Unit On-board Dim Polymer, black. Replacement without tools.

Rotary control for brightness regulation.



**56012.000** ERCO Casambi motion detector with light sensor

for ERCO Minirail 48V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)capable mobile devices.

Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. Minirail adapter for ERCO Minirail 48V track: polymer, black.

Available from 2nd quarter 2023 Black

Weight 0.18kg C€ ⊕ ĽĽ



#### AC003004

Add-on Control Unit Zigbee Polymer, black. Replacement without tools. Control via a Zigbee 3.0 compliant hub.



### 56013.000

ERCO Casambi motion detector with light sensor for ERCO Minirail 48V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)-capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor

Detection range of infrared (PIR) senso 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. Minirail adapter for ERCO Minirail 48V track: polymer, black.

Available from 2nd quarter 2023 Silver

Weight 0.18kg **C €** ⊕ **Ľ**K



AC003001

Add-on Control Unit Casambi Bluetooth Polymer, black. Replacement v

Polymer, black. Replacement without tools.

Control via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)-capable mobile devices or "Casambi Ready" products.