


with transadapter



Hi-trac 3-circuit track

For your regional contact in the ERCO Sales network click here www.erco.com/contact 0.1%-100%

CCR

0.4W

260

Dimming range

LMF

Dimming method

Standby power per control gear

Luminaires per circuit breaker B16

Technical Region: 220-240V 50/60Hz We reserve the right to make technical and design changes. Edition: 28.01.2023 Current version under www.erco.com/A1040770



# Planning data

Melanopic light effect			
Art. no.	Spectrum	MR	MDER
A1040770 (direct)	3000K CRI 97	0.57	0.52

MR Melanopic ratio according to DIN SPEC 5031-100-100:2015-08: "amel;v" MDER Melanopic daylight equivalent ratio according to DIN SPEC 5031-100-100:2015-08: "amel;D65;v"

Multiplying the melanopic ratio MR with the illuminance gives the equivalent melanopic illuminance EML (equivalent melanopic lux). The equivalent illuminance with daylight (D65) is obtained by multiplying the illuminance by the melanopic daylight equivalent ratio MDER.

Cleaning (a) Ambient conditions LMF RSMF	1 P 0.96 0.99	C 0.94 0.97	N 0.90 0.95	D 0.86 0.92	2 P 0.93 0.98	C 0.91 0.97	N 0.86 0.95	D 0.81 0.92	3 P 0.92 0.98	C 0.90 0.97	N 0.84 0.95	D 0.79 0.92	
Hours of operation (h)	1000	5000	10000	20000	30000	40000	50000						

LLMF	1.00	0.99	0.98	0.96	0.94	0.92	0.90
LSF	1	1	1	1	1	1	1

- MF LMFxRSMFxLLMFxLSF
- MF Maintenance Factor
- LMF Luminaire Maintenance Factor
- RSMF Room Surface Maintenance Factor LLMF Lamp Lumens Maintenance Factor
- LLMF Lamp Lumens Maintenance Fac LSF Lamp Survival Factor
- P Room pure
- C Room clean
- N Room normal
- D Room dirty
- b noon any

### Data according to regulations

2019/2020/EU supplemented by 2021/341/EU and 2019/2015/EU supplemented by 2021/340/EU Energy Consumption Labelling Ordinance

This product contains a light source of efficiency class F

Due to thermal and photometric properties as well as to protect electronic components from ESD (electrostatic discharge) the light source cannot be changed by the customer.

ID EPREL: 985715

Model identifier: 3000057845

Download data sheets for control gear and disassembly instructions at www.erco.com/slr

# Technical data in accordance with international norms and standards


IEC 60598	Luminaires – Part 1+2: general requirements, specific
	requirements and tests
IEC 62031	LED modules for general lighting – safety requirements
IEC 62471	Photobiological safety of lamps and lamp systems
EN13032-4	Light and lighting - measurement and representation of
	photometric data
CIE 13	Method of measuring and specifying colour rendering
	properties of light sources

All technical data is subject to industry-standard tolerances. Also see www.erco.com/erco-led

For explanations of the symbols and abbreviations used and other general information, see www.erco.com/symbols



## Accessories



Parscan OnTrack Zoom spotlight A1040770



## Accessories

#### AC002065 Lens unit wallwash Polymer, black lacquered, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



## AC002258

Lens unit narrow framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools. Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black. Aperture.

#### AC002263

Lens unit narrow framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools. Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black. Aperture.



# AC002122 Lens unit zoom spot Polymer, black lacquered, rotatable through 360°. Replacement without tools.

AC002100

Lens unit wallwash

Replacement without tools.

Polymer, white, rotatable through 360°.


Spherolit lens made of optical polymer.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.

# AC002127

Lens unit zoom spot Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.









### Parscan OnTrack Zoom spotlight A1040770

## AC002261

Lens unit wide framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools. 2 projection lenses, continuously focusable. Ideal for short projection distances Framing attachment: stainless steel, black. Aperture.

## AC002266

Lens unit wide framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools. 2 projection lenses, continuously focusable. Ideal for short projection distances. Framing attachment: stainless steel, black Aperture.

# AC006002

Softening lens Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

AC006025 Sculpture lens Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

#### AC002123 Lens unit zoom oval

Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



#### AC002128 Lens unit zoom oval

Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.

4/6



Accessories

AC006009 Cold Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006010 Marbled Meat Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

AC006007 Cold Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

Filter holder: polymer, black, rotatable through 360°. Replacement without

Filter holder: polymer, black, rotatable through 360°. Replacement without

Filter holder: polymer, black, rotatable

through 360°. Replacement without

AC006005

Warm Filter

AC006003

AC006006 Skintone Filter

tools.

tools.

Warm Filter Plus

tools.





AC006004

AC006008

Bread and Pastry Filter

Filter holder: polymer, black, rotatable

Blue Light Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

AC001002 Snoot Polymer, black, coated white on outside.

AC001010 Snoot Polymer, black.

AC004024 Honeycomb anti-glare screen Black

AC006013 Fish Filter tools.

Filter holder: polymer, black, rotatable through 360°. Replacement without



Parscan OnTrack Zoom spotlight A1040770



Accessories

AC005002 Barn doors 4-fold Aluminium, coated black.




55249.000

ERCO Casambi motion detector with light sensor for ERCO 220-240V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. 3-phase adapter for ERCO 220-240V track: polymer, black. Black Weight 0.18kg









### AC007001

AC005004

Barn doors 8-fold Aluminium, coated black.

DALI Casambi Gateway Enables DALI systems to be connected to luminaires, sensors and control units with Casambi Bluetooth. The gateway can only be operated in Evolution networks. Power is supplied exclusively via the DALI bus. Connection via two lines which must be designed for mains voltage. The gateway requires no DALI addresses, the devices appear as non-configured devices in the DALI system. Addressing/commissioning is performed via the DALI control. It can individually control 64 devices, and via the broadcast command up to 249 devices. ČĒ

### 55248.000

ERCO Casambi motion detector with light sensor for ERCO 220-240V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. 3-phase adapter for ERCO 220-240V track: plastic, white.

Weight 0.18kg �� �� C € □ ゐ \!