
Parscan OnTrack Contour spotlight

with transadapter













A1041037 White (RAL9002) LED module: 8.1W 1086lm 4000K neutral white Casambi Bluetooth Version 1 Size S Lens Unit wide framing

Product description


Housing: cast aluminium, powder-coated; can be swivelled through 90° on the bracket. Upper cover made of polymer.

Bracket: cast aluminium/polymer, coated; can be rotated through 360° on the adapter.

Transadapter for ERCO 220-240V track: polymer, white.

ERCO Casambi control gear.
LED module: high-power LEDs. Collimating lens made of optical polymer.
Lens Unit: Aluminium/polymer, coated white, pivotable through 360°. 2 projection lenses, continuously focusable. Ideal for short projection distances. Framing attachment: stainless steel, black. Aperture.

Control via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)-capable mobile devices or "Casambi Ready" products.
Protection Class II
Weight 0.57kg



Measured illuminance levels (new values) E (lx) and maximum edge length D (m) of square projection through framing attachment dependent on projection distance h (m)

h (m)	E (Ix)	D (m)
1	584	0.62
2	146	1.24
3	65	1.86
4	37	2.48
5	23	3.10

Technical data

recimieat auta	
Luminous flux of the luminaire	194lm
Connected load	10.1W
Luminaire efficacy	19lm/W
Colour deviation	1.5 SDCM
Colour rendition index	CRI 82
Lumen maintenance (LED manufacturer	L90/B10 ≤50000h
specifications)	L90 ≤100000h
LED failure rate	0.1% ≤50000h
Dimming range	0.1%-100%
Dimming method	CCR
LMF	E
Standby power per control gear	0.4W
Luminaires per circuit breaker B16	260



Mounting ERCO 3-circuit track Hi-trac 3-circuit track

For your regional contact in the ERCO Sales network click here www.erco.com/contact

Technical Region: 220-240V 50/60Hz We reserve the right to make technical and design changes. Edition: 28.01.2023 Current version under www.erco.com/A1041037



Parscan OnTrack Contour spotlight

Planning data

Melanopic light effect

Art. no. Spectrum MR MDER A1041037 (direct) 4000K CRI 82 0.68 0.62

MR Melanopic ratio according to DIN SPEC 5031-100-100:2015-08: "amel;v"

MDER Melanopic daylight equivalent ratio according to DIN SPEC 5031-100-100:2015-08: "amel;D65;v"

Multiplying the melanopic ratio MR with the illuminance gives the equivalent melanopic illuminance EML (equivalent melanopic lux). The equivalent illuminance with daylight (D65) is obtained by multiplying the illuminance by the melanopic daylight equivalent ratio MDER.

Cleaning (a) Ambient conditions LMF RSMF	1 P 0.96 0.99	C 0.94 0.97	N 0.90 0.95	D 0.86 0.92	2 P 0.93 0.98	C 0.91 0.97	N 0.86 0.95	D 0.81 0.92	3 P 0.92 0.98	C 0.90 0.97	N 0.84 0.95	D 0.79 0.92
Hours of operation (h) LLMF LSF	1000 1.00 1	5000 0.99 1	10000 0.98 1	20000 0.96 1	30000 0.94 1	40000 0.92 1	50000 0.90 1					

MF LMFxRSMFxLLMFxLSF
MF Maintenance Factor
LMF Luminaire Maintenance Factor
RSMF Room Surface Maintenance Factor
LLMF Lamp Lumens Maintenance Factor

LSF Lamp Survival Factor
P Room pure
C Room clean
N Room normal
D Room dirty

Data according to regulations

2019/2020/EU supplemented by 2021/341/EU and 2019/2015/EU supplemented by 2021/340/EU Energy Consumption Labelling Ordinance

This product contains a light source of efficiency class D Due to thermal and photometric properties as well as to protect electronic components from ESD (electrostatic discharge) the light source cannot be changed by the customer.

ID EPREL: 985717

Model identifier: 3000057847

Download data sheets for control gear and disassembly instructions at

www.erco.com/slr

CIE 13

Technical data in accordance with international norms and standards

IEC 60598 Luminaires – Part 1+2: general requirements, specific

requirements and tests

IEC 62031 LED modules for general lighting – safety requirements IEC 62471 Photobiological safety of lamps and lamp systems EN13032-4 Light and lighting – measurement and representation of

photometric data

Method of measuring and specifying colour rendering


properties of light sources

All technical data is subject to industry-standard tolerances. Also see www.erco.com/erco-led

For explanations of the symbols and abbreviations used and other general information, see www.erco.com/symbols

Parscan OnTrack Contour spotlight


Accessories



AC002064

Lens unit spot Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.



AC002063

Lens unit extra wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.




AC002099

Lens unit spot Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



AC002098


Lens unit extra wide flood Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



AC002062

Lens unit flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.



AC002061

Lens unit oval flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.




AC002097

Lens unit flood Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



AC002095


Lens unit oval flood Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



AC002060

Lens unit wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.


Spherolit lens made of optical polymer.



AC002067

Lens unit oval wide flood Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Spherolit lens made of optical polymer.



AC002094

Lens unit wide flood Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.




AC002102

Lens unit oval wide flood Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.

Parscan OnTrack Contour spotlight

Accessories



AC002065

Lens unit wallwash Polymer, black lacquered, rotatable through 360°. Replacement without tools.


Spherolit lens made of optical polymer.



AC002258

Lens unit narrow framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools.

Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black.
Aperture.



AC002100

Lens unit wallwash Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.



AC002263

Lens unit narrow framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools.

Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black.

Aperture.



AC002122

Lens unit zoom spot Polymer, black lacquered, rotatable through 360°. Replacement without

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



AC002261

Lens unit wide framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools.

2 projection lenses, continuously focusable. Ideal for short projection distances

Framing attachment: stainless steel, black.
Aperture.



AC002127

Lens unit zoom spot Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



AC002266

Lens unit wide framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools.

2 projection lenses, continuously focusable. Ideal for short projection distances.

Framing attachment: stainless steel, black.


Aperture.



AC002123

Lens unit zoom oval Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



AC006002


Softening lens

Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC002128

Lens unit zoom oval Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



AC006025

Sculpture lens

Filter holder: polymer, black, rotatable through 360°. Replacement without tools

FRCC

Parscan OnTrack Contour spotlight

Accessories



AC006009 Cold Filter Filter holder: polymer, black, rotatable through 360°. Replacement without




AC006010 Marbled Meat Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools



AC006007 Cold Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006008
Bread and Pastry Filter
Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006005 Warm Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006004 Blue Light Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.




AC006003 Warm Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC004024 Honeycomb anti-glare screen




AC006006 Skintone Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC007001 DALI Casambi Gateway Enables DALI systems to be connected to luminaires, sensors and control units with Casambi Bluetooth. The gateway can only be operated in Evolution networks. Power is supplied exclusively via the DALI bus. Connection via two lines which must be designed for mains voltage. The gateway requires no DALI addresses, the devices appear as non-configured devices in the DALI system. Addressing/commissioning is performed via the DALI control. It can individually control 64 devices, and via the broadcast command up to 249 devices. **C €**



AC006013 Fish Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



Parscan OnTrack Contour spotlight A1041037

Parscan OnTrack Contour spotlight

Accessories



55248.000

ERCO Casambi motion detector with light sensor for ERCO 220-240V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)-capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. 3-phase adapter for ERCO 220-240V track: plastic, white.

Weight 0.18kg **②** △ **(€** □ △ **以**



55249.000

ERCO Casambi motion detector with light sensor for ERCO 220-240V track.
Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)-capable mobile devices.
Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m.
3-phase adapter for ERCO 220-240V track: polymer, black.