




with transadapter









A1041043 White (RAL9002) LED module: 8.1W 862Im 3000K warm white Casambi Bluetooth Version 1 Size S Lens Unit wide framing

#### Product description

Housing: cast aluminium, powdercoated; can be swivelled through 90° on the bracket. Upper cover made of polymer.

Bracket: cast aluminium/polymer, coated; can be rotated through 360° on the adapter.


Transadapter for ERCO 220-240V track: polymer, white.

ERCO Casambi control gear. LED module: high-power LEDs. Collimating lens made of optical polymer. Lens Unit: Aluminium/polymer, coated white, pivotable through 360°. 2 projection lenses, continuously focusable. Ideal for short projection distances. Framing attachment: stainless steel, black. Aperture.

Control via Casambi app (Android/ iOS) with Bluetooth Low Energy (BLE)capable mobile devices or "Casambi Ready" products. Protection Class II Weight 0.57kg

#### Technical data

Luminous flux of the luminaire	154lm
Connected load	10.1W
Luminaire efficacy	15lm/W
Colour deviation	1.5 SDCM
Colour rendition index	CRI 92
Lumen maintenance (LED manufacturer	L90/B10 ≤50000h
specifications)	L90 ≤100000h
LED failure rate	0.1% ≤50000h
Dimming range	0.1%-100%
Dimming method	CCR
LMF	E
Standby power per control gear	0.4W
Luminaires per circuit breaker B16	260



(€ 🐼 🗠 🗆 🐇

Measured illuminance levels (new values) E (Ix) and maximum edge length D (m) of square projection through framing attachment dependent on projection distance h (m)

E (lx) 464 116 52 29	D (m) 0.62 1.24 1.86 2.48
19	3.10
	464 116 52 29



Mounting ERCO 3-circuit track Hi-trac 3-circuit track

For your regional contact in the ERCO Sales network click here www.erco.com/contact

© ERCO GmbH 2023

Technical Region: 220-240V 50/60Hz We reserve the right to make technical and design changes. Edition: 28.01.2023 Current version under www.erco.com/A1041043



Malanania light offeat

## Parscan OnTrack Contour spotlight

### Planning data

Art. no.	Spectrum	MR	MDER
A1041043 (direct)	3000K CRI 92	0.54	0.48

MR Melanopic ratio according to DIN SPEC 5031-100-100:2015-08: "amel;v" MDER Melanopic daylight equivalent ratio according to DIN SPEC 5031-100-100:2015-08: "amel;D65;v"

Multiplying the melanopic ratio MR with the illuminance gives the equivalent melanopic illuminance EML (equivalent melanopic lux). The equivalent illuminance with daylight (D65) is obtained by multiplying the illuminance by the melanopic daylight equivalent ratio MDER.

Cleaning (a) Ambient conditions LMF RSMF	1 P 0.96 0.99	C 0.94 0.97	N 0.90 0.95	D 0.86 0.92	2 P 0.93 0.98	C 0.91 0.97	N 0.86 0.95	D 0.81 0.92	3 P 0.92 0.98	C 0.90 0.97	N 0.84 0.95	D 0.79 0.92	
Hours of operation (h)	1000	5000	10000	20000	30000	40000	50000	0.02	0.00	0.07	0.00	0.02	

LLMF	1.00	0.99	0.98	0.96	0.94	0.92	0.90
LSF	1	1	1	1	1	1	1

- MF LMFxRSMFxLLMFxLSF
- MF Maintenance Factor
- LMF Luminaire Maintenance Factor
- RSMF Room Surface Maintenance Factor LLMF Lamp Lumens Maintenance Factor
- LLMF Lamp Lumens Maintenance Fac LSF Lamp Survival Factor
- P Room pure
- C Room clean
- N Room normal
- D Room dirty
- b noon any

#### Data according to regulations

2019/2020/EU supplemented by 2021/341/EU and 2019/2015/EU supplemented by 2021/340/EU Energy Consumption Labelling Ordinance

This product contains a light source of efficiency class E

Due to thermal and photometric properties as well as to protect electronic components from ESD (electrostatic discharge) the light source cannot be changed by the customer.

ID EPREL: 985714

Model identifier: 3000057844

Download data sheets for control gear and disassembly instructions at www.erco.com/slr

### Technical data in accordance with international norms and standards


IEC 60598	Luminaires – Part 1+2: general requirements, specific
	requirements and tests
IEC 62031	LED modules for general lighting – safety requirements
IEC 62471	Photobiological safety of lamps and lamp systems
EN13032-4	Light and lighting - measurement and representation of
	photometric data
CIE 13	Method of measuring and specifying colour rendering
	properties of light sources

All technical data is subject to industry-standard tolerances. Also see www.erco.com/erco-led

For explanations of the symbols and abbreviations used and other general information, see www.erco.com/symbols



Accessories



Parscan OnTrack Contour spotlight A1041043



#### Accessories

Lens unit wallwash

AC002065

tools.



Lens unit narrow framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools. Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black. Aperture.



AC002100 Lens unit wallwash Polymer, white, rotatable through 360°. Replacement without tools. Spherolit lens made of optical polymer.

Polymer, black lacquered, rotatable

through 360°. Replacement without

Spherolit lens made of optical polymer.



## without tools.

AC002263

Lens unit narrow framing

Aluminium/polymer, coated black, pivotable through 360°. Replacement

Projection lens, continuously focusable. Ideal for long projection distances. Framing attachment: stainless steel, black. Aperture.



AC002122 Lens unit zoom spot Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.

AC002127

Lens unit zoom spot Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.









### AC002261

Lens unit wide framing Aluminium/polymer, coated white, pivotable through 360°. Replacement without tools. 2 projection lenses, continuously focusable. Ideal for short projection distances Framing attachment: stainless steel, black. Aperture.

### AC002266

Lens unit wide framing Aluminium/polymer, coated black, pivotable through 360°. Replacement without tools. 2 projection lenses, continuously focusable. Ideal for short projection distances. Framing attachment: stainless steel, black Aperture.

### AC006002

Softening lens Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

AC006025 Sculpture lens Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



### AC002123


Lens unit zoom oval Polymer, black lacquered, rotatable through 360°. Replacement without tools.

Anti-reflective zoom lens made of optical polymer, infinitely variable focus.



### AC002128

Lens unit zoom oval Polymer, white, rotatable through 360°. Replacement without tools. Anti-reflective zoom lens made of optical polymer, infinitely variable focus.





Accessories

### AC006009

Cold Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



AC006010 Marbled Meat Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.





### AC006004

AC006008

tools.

Bread and Pastry Filter

Filter holder: polymer, black, rotatable

through 360°. Replacement without

Blue Light Filter Filter holder: polymer, black, rotatable through 360°. Replacement without tools.




AC006003

Filter holder: polymer, black, rotatable through 360°. Replacement without

Filter holder: polymer, black, rotatable through 360°. Replacement without







#### AC007001

AC004024

Black

Honeycomb anti-glare screen

DALI Casambi Gateway Enables DALI systems to be connected to luminaires, sensors and control units with Casambi Bluetooth. The gateway can only be operated in Evolution networks. Power is supplied exclusively via the DALI bus. Connection via two lines which must be designed for mains voltage. The gateway requires no DALI addresses, the devices appear as non-configured devices in the DALI system. Addressing/commissioning is performed via the DALI control. It can individually control 64 devices, and via the broadcast command up to 249 devices. **C E** 

AC006013 **Fish Filter** Filter holder: polymer, black, rotatable through 360°. Replacement without tools.

AC006006

tools.

Skintone Filter

tools.

AC006005

Warm Filter

Warm Filter Plus Filter holder: polymer, black, rotatable through 360°. Replacement without tools.



#### Accessories

#### 55248.000

ERCO

ERCO Casambi motion detector with light sensor for ERCO 220-240V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. 3-phase adapter for ERCO 220-240V track: plastic, white. White Weight 0.18kg



#### 55249.000

ERCO Casambi motion detector with light sensor for ERCO 220-240V track. Setup via Casambi app (Android/iOS) with Bluetooth Low Energy (BLE)capable mobile devices. Use for daylight-dependent light control with or without motion detector. Detection range of infrared (PIR) sensor 100°/ 5m. At 3m room height, this is a circle with diameter of approx. 7m. 3-phase adapter for ERCO 220-240V track: polymer, black. Black Weight 0.18kg ∰ ♠ C € □ ♠ ¥